PRETREATmaker Basic





TO UPGRADE YOUR PRETREATMENT CAPABILITIES, CONTACT BROTHER DTG AT 866-750-2542 OR VISIT Brother DTG.com.





| Spraying area | 15.7 × 17.7" (40 × 45 cm) |
|---------------------------------|--|
| Spraying method | Nozzle is moving over the table (inside) |
| Table length | 24.4" (62 cm) |
| Spray direction | Uni / Bi-Directional |
| Nozzles | 1 Nozzle |
| Number of bottles | Two Pretreat (2 Liter Bottles), One Water (2 Liter), One Waste (2 Liter) |
| Motor | Stepper Motor |
| Pumps | One pump |
| Dimensions | L 27.5" × W 20.5" × H 22.0" (L 70 × W 52 × H 56 cm) |
| Dimensions (transport) | L 31.5" × W 22.8" × H 28.7" (L 80 × W 58 × H 73 cm) |
| Weight | 84 lbs. (38 kg) |
| Weight (transport) | 104 lbs. (47 kg) |
| Connection | 220/230 or 110/120 VAC (automatic switch) |
| Consumption | 150 W |
| Operating pressure (precoating) | max. 7 bar |
| Included in delivery | replacement nozzle, replacement filter and ultrasound cleaner |
| Additional characteristics | zinc- and powder-coated housing |











- 1. Schulze Pretreat Cleaner 807068
- 2. Nozzle (green) TP9501EVS
- 3. Filter 807015

- 4. 0-ring washer 803368
- 5. Quick exchange cap 803368

